



# Future Coat Technology

## STRIP X 730 GOLD

Strip X 730 is capable to strip gold layer without the damage on the lower copper and nickel layer

Solution composition and operative conditions:

	Optimum	Range
Gold stripper	g/L 40g	25g-50g
KCN	g/L 40g	45g-60g
Temperature	°C 27	20-40

Strip x 730 velocity (27°C)	μ/min 1.5
Strip x 730 bath	PVC liner tank or stainless steel tank
Heating	stainless steel heating pipe
Mixture	Cathode movement
Ventilation	Necessary

## 2. Preparation method

- (1) Clean gold-stripping bath completely, and fill pure water with ½ required volumes;
- (2) Add KCN in proportion to mix and dissolve;
- (3) Add gold-stripper with the required volume, to mix evenly.
- (4) Fill pure water to specified volume.

## 3. Maintenance

When the gold-stripping velocity is slow, gold stripper should be supplemented;

